

QuickMover and QuickBar

Feather-light and gentle moving, perfect positioning and stable measurement



Base plate vertical

QuickMover - Protects the granite slab and makes handling feather-light

At the push of a button, the rotary table can be moved or shifted almost weightlessly and brought smoothly and safely into position. When released, the rotary table is held firmly and securely.

Technical data

- Integrated mini-compressor
- Air cushion approx. 0.009mm
- Parallelism of precision stop to rotary axis 0.001 mm/100 mm
- Center height raised by 15 mm

Items included in delivery

- QuickMover adapter plate with precision-ground AirFlow nozzles
- Integrated precision stop with 2 balls per side
- Built-in manual pushbutton



QuickProcess: briefly probe with measuring probe, then the rotary table moves to the next position – without M-link or integration in the machine control system

Pushbutton for activating the air cushion

Emergency stop (on EA-508 Q-Line only)

Item No.

Item No.	Designation
MET.Q0x-M	QuickMover for EA-50x
MET.Q0x-Mk	QuickMover compact for MA-50x
MET.Q0x-P	QuickProcess

QuickBar - Align quickly and reliably



Items included in delivery

- Alignment bar with precision notches, for surface or edge mounting
- For hole spacing 200 and 300 mm
- Adapter for thread M10 + M12
- If thread in granite is available, direct mounting is possible.

MA-508.m-Q with stop bar for edge mounting, can be mounted without holes (adhesive can be removed without leaving residue)

Item No.

Item No.	Designation
MET.Q0x-Bar-F	QuickBar for edge mounting
MET.Q0x-Bar-W	QuickBar for surface mounting

EA-508.R-Q with stop bar for surface mounting, hole spacing 200 mm, can also be mounted without holes (adhesive can be removed without leaving residue)

QuickControl with Microsoft tablet

Easy to operate, stand-alone or automated with M-function



ControlTablet MT – can be easily mounted anywhere and brought into operating position

Easy control via peak interface. Can be mounted anywhere, while equipped with both a suction cup and magnet. Easy to operate, lightweight and universal. Particularly handy in the shopfloor area as well.

Technical data


- Win10 Pro
- Intel Celeron N4120 processor, 4 MB cache, max. 2.6 GHz
- L 300 x W 200 x D 50 mm
- Display 11.6" / resolution 1920 x 1080 pixels

Items included in delivery

- ControlTablet, incl. operating system
- Charger
- USB Bluetooth dongle for pL iBox
- Anodized tablet holder with magnets and suction cup
- USB docking station with Ethernet, video, HDMI etc
- QuickControl software, basic or pro
- TeamViewer
- blackBOXcom
- Camera
- Set-up instructions A4



Tablet holder with suction cup or magnet.



QuickDock – the perfect interface for supplementary locator systems e.g. from DK.

QuickControl PROFI - fully automatable without integration



- Manual operation
- Referencing
- Angle
- Indexing calculator
- Absolute / incremental / endless
- Zeroing at each position
- Programming mode
- Program memory
- External control via M-function (fully automatic sequence via machine control)



QuickBox – high-quality box made of white leather for safe and careful transport



QuickShell – high-quality cover made of leather for protection from dust and impact if rotary table is parked

Item No.

Item No.	Designation
CNC.C-digi	Version digital
CNC.C-pro	Version professional
CNC.PFB-Ct	Box for potential isolation
CNC.Tablet	ControlTablet
MET.Q0x Box	QuickBox
MET.Q0x-D08	QuickDock M8, 15 mm spacing
MET.Q0x-D10	QuickDock M10, 15 mm spacing
MET.Q0x-S	QuickShell for EA-50x
MET.Q0x-Sk	QuickShell compact for MA-50x